

INDUSTRIAL COMPONENT DATA

MAP0312030PER5 ELDON Wall mounted, 300x1200x300

Brand: ELDON | Manufacturer Part Number: MAP0312030PER5



Manufacturer	ELDON
MPN / Reference	MAP0312030PER5
Catalog number	0312030
Category	Enclosure/switchgear cabinet (empty)
Minimum order	1 Pcs
Document ID	EO-BDE6A8ECCB
Generated	2026-07-31

Product Overview

Wall mounted, 300x1200x300

Mural, 300x1200x300, compact, 1-door, no MP, mild steel, IP66

Wall mounted, 300x1200x300, Compact enclosure, 1-door, no MP, mild steel, IP66

STRUCTURED PRODUCT DATA

Technical Specifications

No structured technical attributes are currently available. Submit an RFQ for technical review.

Classification & Catalog Path

Catalog path ELDON > Steel Wall Mounting Enclosures

Additional Product Information

Features

Material: Body: 1.5 mm mild steel. Gland plate: 1.4 mm mild steel. Door: 1.5 mm mild steel MAP0306030R5 / 2 mm MAP0308030R5 and above. Mounting plate: 2 mm galvanized steel.

Body: Folded and seam welded. Four 8.5 mm diameter holes for wall fixing, pressed out in 20.4 mm diameter × 2 mm depressions, to allow air circulation around the rear part of the enclosure.

Front panel: Surface mounted with 130° opening. Concealed removable hinges with captive pin. Hinges can be mounted to allow top or bottom opening. Mechanical door stop keeps the panel open. Inner M6 welded studs. One removable mounting profile on the hinge side. Sealing is ensured by an injected one piece polyurethane gasket.

Lock: Customized lock with double-bit for easy opening of the panel. Double-bit 3 mm insert and 90° movement. Other inserts are available as an accessory.

Mounting plate: The mounting plate is marked vertically at 10 mm intervals, for easy horizontal positioning of equipment. On the top and bottom there are holes to facilitate cable fixing. Fixed onto M8 press welded studs to the rear of the enclosure.

All sides, from 800 mm and above, are strengthened by folded edges.

Gland Plate Opening: In top and bottom. Situated at the far rear of the enclosure, to make cabling onto the mounting plate

easier. Gland plates (AF) and gaskets (AG) are not included. If the MAP panel is to be combined to an MAS or MAD enclosure, then the gland plate from the MAS/MAD enclosure can be used with the MAP pane...

REQUEST PRICE, AVAILABILITY & TECHNICAL REVIEW

Send ELDON / MAP0312030PER5 with the required quantity to info@electricaonline.com or use electricaonline.com/request-quote.

GLOBAL OFFICES

Germany: Lise-Meitner-Straße 13, 89081 Ulm | USA: 16225 Park Ten Pl #500, Houston, TX 77084 | UAE: HDS Business Centre Tower, Cluster M, 33rd Floor, JLT, Dubai

Catalog-generated document. Product names, marks and specifications belong to their respective owners. Verify safety-critical, compatibility and certification requirements against the manufacturer documentation before purchase or installation.